

KIMBLE® Plain Disposable Borosilicate Glass Tube, 10 x 75mm, 4 mL

- Complies with ASTM Specification E890
- Manufactured from borosilicate glass 5.1
- 51 expansion borosilicate glass offers excellent chemical resistance against sodium leaching, a factor common in soda lime glass products
- Tubes are packed in convenient trays for ease of use on bench tops and in drawers
- The 6 x 50 mm size is often referred to as a "Durham tube"
- Trays are shrink-wrapped in plastic film, with tubes remaining in constant alignment for protection against in-transit breakage and contamination
- No marking spot

Catalog Number: **73500-1075**

Product Overview

These premium quality tubes feature sturdy, uniform bottoms and consistent lengths. The 10 x 75 and 12 x 75 mm sizes are suitable for cell washing procedures.

Specifications

Length (mm)	75
OD (mm)	10
Capacity (mL)	4
Quantity	1000
Shelf Pack Quantity	250

Learn about the physical and chemical properties of our glass, plastic and rubber materials.

[**View Technical Information**](#)

This information is accurate as of 11/07/2025 and is subject to change.

