

RELATIONSHIP REDEFINED THE PARTNERSHIP YOU DESERVE



GIA™ Stapler with DST Series™ Technology
Product Brochure

Medtronic
Further, Together



**RELIABILITY.
CONSISTENCY.
EFFICIENCY.**



At Medtronic, we address your most pressing needs.

As a complete solution provider, we offer a comprehensive open stapling portfolio with a reputation for reliability, consistency, and efficiency.

Partner with us for:

- Products designed to meet all of your procedural and economic needs
- Efficient inventory-cost management
- Hands-on training by highly trained clinical experts
- Expertise from a global network of healthcare professionals
- On-site support from a skilled sales force


We help you deliver the best patient care you can by providing access to a broad range of innovative technology, from wound closure to advanced energy solutions.

By collaborating with Medtronic, you'll experience a relationship redefined.

Ready to learn all about the GIA™ stapler with DST Series™ technology, one of our colorectal and thoracic solutions? Read on...

GIA™ STAPLER WITH DST SERIES™ TECHNOLOGY FEATURES

This linear cutting stapler designed with DST Series™ technology 4.8 mm, 3.8 mm, 2.5 mm staple heights may improve staple formation and increase resistance to leakage.¹



LOCKOUT

Covers blade before and after firing and prevents accidental pre-firing before clamping



DISPOSABLE LOADING UNIT

With secure grip. New blade with each firing

PINLESS ANVIL

For atraumatic placement



INLAY GRIPS

For ergonomics and firing force



QUICK RELEASE BUTTON

For easy unclamping and removal of forks



ADJUSTABLE FIRING KNOB

Gives surgeons the ability to fire from either side of the instrument

CARTRIDGE LOCK LEVER

For access



440 STAINLESS STEEL BLADE

With each cartridge


REAR OR CENTER HINGE CLAMPING

For one-handed positioning




PORTFOLIO + STANDARDIZATION + SERVICE

DST SERIES™ TECHNOLOGY




TRADITIONAL STAPLE

Round wire cross-section is more prone to bend in any direction in challenging applications.



DST SERIES™ TECHNOLOGY

Rectangular wire cross-section bends more reliably in the intended direction



GIA™ STAPLER WITH DST SERIES™ TECHNOLOGY

SINGLE USE STAPLER

PRODUCT SPECIFICATIONS

Stapler	Product Description	Cartridges Available	Staple Length Before Closure	Approx. Staple Height Closed	Color Coded	Number Of Reloads/ Total Number Of Firings	Number Of Staples	Rows Of Staples	Length Of Staple Line
GIA6025S	GIA™ Stapler with DST Series™ Technology 60 mm	GIA6025L	2.5 mm	1.0 mm	White	7/8	64	4	66 mm
GIA6038S	GIA™ Stapler with DST Series™ Technology 60 mm	GIA6038L	3.8 mm	1.5 mm	Blue	7/8	64	4	66 mm
GIA6048S	GIA™ Stapler with DST Series™ Technology 60 mm	GIA6048L	4.8 mm	2.0 mm	Green	7/8	64	4	66 mm
GIA8038S	GIA™ Stapler with DST Series™ Technology 80 mm	GIA8038L	3.8 mm	1.5 mm	Blue	7/8	84	4	86 mm
GIA8048S	GIA™ Stapler with DST Series™ Technology 80 mm	GIA8048L	4.8 mm	2.0 mm	Green	7/8	84	4	86 mm
GIA10038S	GIA™ Stapler with DST Series™ Technology 100 mm	GIA10038L	3.8 mm	1.5 mm	Blue	7/8	104	4	106 mm
GIA10048S	GIA™ Stapler with DST Series™ Technology 100 mm	GIA10048L	4.8 mm	2.0 mm	Green	7/8	104	4	106 mm



RELATIONSHIP REDEFINED

THE PARTNERSHIP YOU DESERVE



1 Rodeheaver, Directional Stapling Technology: Improved Reliability in Staple Formation in canine models (DST Series™ GIA™ Stapler), 2006. M121186

Medtronic



Use scan app to read

For more information, please visit
medtronic.eu/product-catalog

IMPORTANT: Please refer to the package insert for complete instructions, contraindications, warnings and precautions.

© 2016 Medtronic. All rights reserved. Medtronic, Medtronic logo and Further, Together are trademarks of Medtronic. All other brands are trademarks of a Medtronic company. 16-eu-dst-gia-product-brochure-995508