

Original Perfusor® Lines

Original Perfusor® Line Type PCA with BCV and slite clamp	PVC (DEHP-free)	Inner diameter (mm)	Length (cm)	Sales Units / Pcs.	Code No. (REF)
	▪	1.5	150	100	8726019
Original Perfusor® Lines	PVC-Free (PE)	Inner diameter (mm)	Length (cm)	Sales Units / Pcs.	Code No. (REF)
	▪	0.9	50	100	8255059
	▪	0.9	100	100	8255067
	▪	0.9	300	100	8250146
	▪	0.9	250	100	8272565
	▪	0.9	200	100	8723060
	▪	0.9	150	100	8722935
Original Perfusor® Line	PVC-Free (PE)	Inner diameter (mm)	Length (cm)	Sales Units / Pcs.	Code No. (REF)
	▪	0.9	150	100	8723010