

## Remote alarm thermo-hygrometer, Traceable®

These thermo-hygrometers are ideal for routine measurements, monitoring 'round the clock', all quality control needs, and critical experimental requirements. Perfect for use in hoods, classrooms, stockrooms, environmental chambers and chemical storage areas.

- Triple-display shows min., max. and current humidity/temperature readings
- Min./max. temperature and humidity memories
- High/low alarm feature may be set by user in 1% RH or 1° increments
- F/°C switchable
- Remote humidity/temperature sensor on a 2,1 metre cable

\* Temperature

\*\* Humidity

\*\*\*Temperature probe

Individually calibrated ISO 17025 certified. Individually certified—traceable to NIST

Supplied with Traceable® certificate, battery, external sensor, flip-open stand and wall mount.



Description	Range	Accuracy	Resolution	WxDxH (mm)	Pk	Cat. No.
Remote alarm RH/temperature monitor with external probe 2,1 m cable (external and ambient readings)	0...60 °C* 5 - 95 %**	±3% (RH: 25 - 75%), ±5% ±5***	0,1* 0,1%**	69×19×102	1	620-2486
Remote alarm RH/temperature monitor with internal probe (ambient reading only)	0...60 °C* 5 - 95 %**	±3% (RH: 25 - 75%), ±5% ±5***	0,1* 0,1%**	69×19×102	1	620-2487