

ACCESSORIES



## Meritans DTXPlus® Accessories

Sterile, single use

PRODUCT CODE	MALE/FEMALE OR MALE/MALE LINE CONNECTION	TUBING LENGTH	LINE COLOUR CODING	BOX/CASE CONTENT (UNITS)	PRIMING VOLUME (CM <sup>3</sup> /CM)	TUBE DIAMETER INNER (MM)	OUTER (MM)
<b>PRESSURE LINES (PVC)</b>							
682226	M/F	25cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682229	M/F	100cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682230	M/F	150cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682232	M/F	200cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682234	M/M	100cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682079	M/M	150cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682236	M/M	200cm	Clear	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
682237	M/F	100cm	Red	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
685185	M/F	150cm	Red	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
685190	M/M	125cm	Blue	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
685171	M/M	150cm	Blue	25/250	0.019	1.575 (± 0.076)	3.175 (± 0.051)
686619	M/F	150cm	Yellow	25/125	0.019	1.575 (± 0.076)	3.175 (± 0.051)
<b>CONNECTA PE PRESSURE MONITORING LINES (POLYETHYLENE)</b>							
682194	M/F	15cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682185	M/F	50cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682189	M/F	100cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682191	M/F	150cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682192	M/F	200cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682186	M/M	50cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682190	M/M	100cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)
682193	M/M	200cm	Clear (Red/Blue Stickers)	25/250	0.011	1.20 (± 0.05)	2.50 (+ 0.1/- 0.05)

**PRODUCT CONTENTS**

- Pressure Lines (PVC) for accurate transmission of the pressure waveform
- PVC Pressure Lines maximum pressure tolerance (fluid filled) 200 psi
- Connecta PE (PolyEthylene) lines as a non PVC alternative
- Colour coded stickers supplied with Connecta PE to facilitate line identification
- Connecta PE Pressure Lines maximum pressure tolerance (fluid filled) 43 psi

**PRESSURE ACCESSORIES (NON-STERILE)**

PRODUCT CODE	MODEL	DESCRIPTION	BOX/CASE CONTENT (UNITS)
682093	TBG	Transducer BackGround for pole mounting (up to 4 transducers)	10/100
682274	TMM	Snap-On TMM Cable Organiser	5/50
682275	TMM/TBG	TBG with Snap-On TMM Cable Organiser (P/Ns 682093, 682274)	5/50
10026379	'O' Ring	Replacement 'O' Ring for Interface Cable	50
684003	Cable Checker	Transducer tester for monitor calibration	1
682104	UMM	Universal Manifold Mount	5/50