

Novocent / Novocent Protekt**

Central Venous Catheters

- Complete range of Central Venous Catheters, single, double, triple & quadruple lumen, meeting the needs of intensive care and emergency medication
- The Multi-lumen catheters prevent the mixing of incompatible drugs thus minimizing the complications

Kit Contents

- Indwelling catheter
- Y-Introducer needle with valve
- J-Tip guide wire (Nitinol)
- Dilator
- Luer lock syringe
- Scalpel
- Catheter holder
- Catheter holder clamp

Common Features

- Central Venous Catheter made of bio-compatible Polyurethane material provides strength during insertion and also softens at body temperature to conform to the body tissues and reduces the risk and vascular trauma
- Specially designed soft & bevelled tip for smooth & easy insertion of catheter
- Soft Flexible J-Tip Guide wire prevents the vessel perforation and also provides good torque to ensure firm insertion
- Radio-opaque material of catheter with clear, definite marking facilitates correct placement of catheter tip

**Novocent Protekt available with needle free connector which provides closed system & lipid resistant three way stop cock

Sr. No.	Generic Name of Device	Brand Name of Device	Product Code
1	Central Venous Catheter Single Lumen	Novocent	15001-15025, 15031-15049, 15350
		Novocent protekt	17000-17023, 18050-18064
2	Central Venous Catheter Double Lumen	Novocent	15050-15069, 15071, 15085-15099, 15361-15363
		Novocent protekt	17030-17050, 18070-18082
3	Central Venous Catheter Triple Lumen	Novocent	15100-15117, 15150-15163
		Novocent protekt	17055-17073, 18085-18093
4	Central Venous Catheter Quintuple Lumen	Novocent	17271-17272
		Novocent protekt	17260-17270, 18100-18102, 18110-18112



15100-15603

Also available with:



Guiding Syringe



Needle Free Connector

Central Venous Catheters Sizes

PRODUCT DESCRIPTION		INDWELLING CATHETER		GUIDE WIRE	
Variant	Novocent	Specification (Sizes)	Length (mm)	Diameter (inch/mm)	Length (cm/mm)
Single Lumen	15001	3FR / 20G (D)	80	0.018 / 0.46	50/500
	15002	3FR / 20G (D)	130	0.018 / 0.46	50/500
	15003	3FR / 20G (D)	150	0.018 / 0.46	50/500
	15004	3FR / 20G (D)	160	0.018 / 0.46	50/500
	15005	3FR / 20G (D)	200	0.018 / 0.46	50/500
	15006	4FR / 18G (D)	130	0.018 / 0.46	50/500
	15007	4FR / 18G (D)	150	0.018 / 0.46	50/500
	15008	4FR / 18G (D)	160	0.018 / 0.46	50/500
	15009	4FR / 18G (D)	200	0.018 / 0.46	50/500
	15010	5FR / 16G (D)	160	0.035 / 0.89	50/500
	15011	5FR / 16G (D)	200	0.035 / 0.89	50/500
	15012	5FR / 16G (D)	300	0.035 / 0.89	70/700
	15013	6FR / 14G (D)	160	0.035 / 0.89	50/500
	15014	6FR / 14G (D)	200	0.035 / 0.89	50/500
	15015	6FR / 14G (D)	300	0.035 / 0.89	70/700
	15016	7FR / 12G (D)	160	0.035 / 0.89	50/500
	15017	7FR / 12G (D)	200	0.035 / 0.89	50/500
	15019	8FR / 12G (D)	200	0.035 / 0.89	50/500
	15020	9FR / 11G (D)	200	0.035 / 0.89	50/500
Double Lumen	15068	4FR / 22G (P) - 22 G (D)	80	0.018 / 0.46	50/500
	15050	4FR / 22G (P) - 22 G (D)	130	0.018 / 0.46	50/500
	15051	4FR / 22G (P) - 22 G (D)	160	0.018 / 0.46	50/500
	15052	4FR / 22G (P) - 22 G (D)	200	0.018 / 0.46	50/500
	15069	5FR / 20G (P) - 18 G (D)	80	0.018 / 0.46	50/500
	15053	5FR / 20G (P) - 18 G (D)	130	0.018 / 0.46	50/500
	15064	5FR / 20G (P) - 18 G (D)	160	0.018 / 0.46	50/500
	15054	5FR / 20G (P) - 18 G (D)	200	0.018 / 0.46	50/500
	15055	7FR / 16G (P) - 16 G (D)	160	0.035 / 0.89	50/500
	15056	7FR / 16G (P) - 16 G (D)	200	0.035 / 0.89	50/500
	15057	7FR / 16G (P) - 16 G (D)	300	0.035 / 0.89	70/700
	15058	7FR / 14G (P) - 18 G (D)	160	0.025 / 0.64	50/500
	15059	7FR / 14G (P) - 18 G (D)	200	0.025 / 0.64	50/500
	15060	7FR / 14G (P) - 18 G (D)	300	0.025 / 0.64	70/700
	15065	7FR / 18G (P) - 14 G (D)	160	0.035 / 0.89	50/500
	15066	7FR / 18G (P) - 14 G (D)	200	0.035 / 0.89	50/500
	15061	8FR / 14G (P) - 14 G (D)	160	0.035 / 0.89	50/500
	15063	8FR / 14G (P) - 14 G (D)	300	0.035 / 0.89	70/700
Triple Lumen	15106	4.5FR / 23G (P) 20G (D)-23G(M)	60	0.018 / 0.46	50/500
	15115	4.5FR / 23G (P) 20G (D)-23G(M)	80	0.018 / 0.46	50/500
	15116	4.5FR / 23G (P) 20G (D)-23G(M)	130	0.018 / 0.46	50/500
	15108	5FR / 22G (P) 20G (D)-22G(M)	80	0.018 / 0.46	50/500
	15109	5FR / 22G (P) 20G (D)-22G(M)	130	0.018 / 0.46	50/500
	15110	5FR / 22G (P) 20G (D)-22G(M)	150	0.018 / 0.46	50/500
	15111	5FR / 22G (P) 20G (D)-22G(M)	160	0.018 / 0.46	50/500
	15112	5FR / 22G (P) 20G (D)-22G(M)	200	0.018 / 0.46	50/500
	15100	5.5FR / 22G (P) 20G (D)-22G(M)	80	0.018 / 0.46	50/500
	15101	5.5FR / 22G (P) 20G (D)-22G(M)	160	0.018 / 0.46	50/500
	15102	5.5FR / 22G (P) 20G (D)-22G(M)	200	0.018 / 0.46	50/500
	15113	7FR / 18G (P) 16G (D)-18G(M)	150	0.035 / 0.89	50/500
	15103	7FR / 18G (P) 16G (D)-18G(M)	160	0.035 / 0.89	50/500
	15104	7FR / 18G (P) 16G (D)-18G(M)	200	0.035 / 0.89	50/500
	15105	7FR / 18G (P) 16G (D)-18G(M)	300	0.035 / 0.89	70/700
Four Lumen	-	8FR / 18G (P) 16G (D)-18G(M1-M2)	130	0.035 / 0.89	50/500
	-	8FR / 18G (P) 16G (D)-18G(M1-M2)	160	0.035 / 0.89	50/500
	-	8FR / 18G (P) 16G (D)-18G(M1-M2)	200	0.035 / 0.89	50/500